
AccuRate®

PRECISION PUMP SETTING GAUGE



APPLICATION:

Kenco AccuRate® Pump Setting Gauges utilize precision scientific glass to provide the most accurate reading possible for calibrating the flow rate of a chemical metering pump. They are also used to periodically monitor the performance and accuracy of a chemical injection system. The AccuRate® gauge can also be used as the primary containment reservoir of a fluid that will be pumped into a chemical injection system.




THE ONE-MINUTE TEST:


To check the pumping rate of a chemical pump, isolate the chemical in the tank from the AccuRate® gauge. The decal on the gauge glass has (2) individual calibrated scales. The scale on the left side is a volume scale in milliliters; in a one-minute test, the scale will read the pump rate in milliliters. The scale on the right side will depend on what type of flow rate is required; i.e. U.S. Gallons Per Day (USG), Gallons Per Hour (GPH), Liters Per Day (LPD), or Liters Per Hour (LPH). Keep the isolating valve closed and observe the number of marks the fluid level passes in one minute. This will give you the actual chemical pump rate. If the rate is not the one desired, make an adjustment to the chemical pump feed rate and conduct as many one-minute tests as is necessary to set the chemical pump rate to the rate desired.

GAUGE FEATURES:

- Precision borosilicate glass sight tube delivers precision rate calibration from 0.05% to 0.2%. AccuRate® Pump Setting Gauges will calibrate pump rates up to 1095 Gallons Per Day (GPD) or 4,140 Liters Per Day (LPD).
- 2. Clear polycarbonate shield for high impact resistance is now standard
- 3. Five (5) scale options are available: U.S. Gallons By Volume (USG), Gallons Per Day (GPD), Gallons Per Hour (GPH), Liters Per Day (LPD) and Liters Per Hour (LPH) Standard volumetric scale in ML on all units
- 4. Tubing connector on top of gauge is supplied with every unit
- 5. Standard end plate materials are 316 SS and PVC. Other materials are available upon request.
- 6. Drain holes in lower end plate eliminate condensation

COMMON APPLICATION FOR AccuRate® PUMP SETTING GAUGE





AccuRate® PUMP SETTING GAUGE SPECIFICATIONS

GAUGE MODEL NUMBER	END PLATE MATERIAL	GAUGE VOLUME		MAXIMUM PUMPING RATE (BASED ON A 1 MINUTE TEST)				INLET PORT	END PLATE
		ML	USG	GPH	GPD	LPH	LPD	SIZE	O.D.
PSG0180-S	316 S.S.	180	0.0476	2.84	68.5	10.8	258	1/2"	2-7/8"
PSG0180-P	PVC								3"
PSG0404-S	316 S.S.	404	0.107	6.4	154	24. 3	580	3/4"	3-3/8"
PSG0404-P	PVC								3-1/2"
PSG0720-S	316 S.S.	720	0.19	11.4	274	43.2	1035	1"	3-7/8"
PSG0720-P	PVC								4"
PSG1620-S	316 S.S.	1620	0.428	25.6	615	97	2330	1"	4-7/8"
PSG1620-P	PVC								5"
PSG2880-S	316 S.S.	2880	0.76	45.6	1095	172	4140	1"	5-7/8"
PSG2880-P	PVC								6"

- Gauge Glass Repair Kit consists of O-ring Seals and Sight Tube with Calibration Scale.
- To order a Gauge Glass Repair Kit, add suffix "-RK" to Gauge Model Number. (Example: PSG0180-S-V-GPH-RK).

ORDERING SYSTEM **AccuRate® Pump Setting Gauge** RE UESTED BY: _ COMPANY:___ _ STATE:_____ IP:___ CITY: __ ADDRESS:_ PHONE:_ _ FA :__ ___ EMAIL : __ Gauge Model Number: **End Plate Material: Gasket Material: Calibration Scale:** PSG0180 16 Stainless Steel A = AflasUSG US Gallons by Volume PSG0 0 PVC В Buna-N GPH **Gallons Per Hour** PSG0720 Other (Please specify above) Ε **Ethylene Propylene GPD Gallons Per Day** PSG1620 Fluorocarbon LPH **Liters Per Hour** PTFE Envelope LPD Liters Per Day PSG2880 Neoprene Filler

Example Order Number: PSG0180-S-V-GPH

Please contact Kenco to re uest a uote for options not covered by gauge specifications shown above.

For a Redline glass strip, add - RL to end of part number